


















MONTAGEANLEITUNG

-  MONTAGEANLEITUNG
-  ASSEMBLY INSTRUCTION
-  DE INSTRUCTIE VAN DE ASSEMBLAGE
-  ISTRUZIONE DELL'ASSEMBLEA
-  INSTRUCCIÓN DE ASAMBLEA
-  INSTRUCTION DE MONTAGE
-  NÁVOD K MONTÁŽI
-  MONTERINGSANVISNING

-  MONTAJ TALIMATI
-  ASENNUSOHJE
-  BRUGSANVISNING
-  BRUKSANVISNING
-  UPUTE ZA MONTAŽU
-  NAVODILA ZA MONTAŽO
-  SZERELÉSI ÚTMUTATÓ
-  INSTRUCTIUNI DE MONTAJ



Version 16.6

Modell-Nr.

12160

ART.-NR. FRONT KORPUS

12162

Rot
(ähnl. RAL 3002)

Silber

12167

Ultramarinblau
(RAL 5002)

Silber

12166

Silber

Schwarz
(RAL 9005)

Friedrich Küpper GmbH
Friedrich-Küpper-Weg
54570 Berlingen
Deutschland

Telefon +49 (0) 65 91 - 95 42 0
Telefax +49 (0) 65 91 - 95 42 17
E-Mail info@friedrich-kuepper-gmbh.de
Internet www.friedrich-kuepper-gmbh.de

EINZELTEILE / PIECES

1× **A**



1766 mm × 465 mm

Art.-Nr. E0527 (Silber/silver)

Art.-Nr. E0528 (Schwarz/black)

1× **B**



467 mm × 232 mm

Art.-Nr. E0529 (Silber/silver)

Art.-Nr. E0530 (Schwarz/black)

1× **C**




692 mm × 146 mm

Art.-Nr. E0531 (Silber/silver)

Art.-Nr. E0532 (Schwarz/black)

3× **D**



462 mm × 143 mm

Art.-Nr. E0533 (Silber/silver)

Art.-Nr. E0534 (Schwarz/black)

1× **E**




698 mm × 146 mm

Art.-Nr. E0537 (silber/silver)

Art.-Nr. E0535 (rot/red)

Art.-Nr. E0536 (blau/blue)

2× **X**



450 mm × 20 mm

Art.-Nr. E0789 (Schwarz/black)

1× **Y**





Art.-Nr. E0422 (Schwarz/black)

BEUTELINHALT / BAG CONTENT

 <p>10× M5 × 10 mm Art.-Nr. E0286</p>	 <p>10× ø 5,3 mm Art.-Nr. E0287</p>	 <p>10× M5 Art.-Nr. E0288</p>	 <p>20× M4 × 10 mm Art.-Nr. E0289</p>	 <p>20× M4 Art.-Nr. E0290</p>	 <p>2× KU 4 × 16 mm Art.-Nr. E0285</p>
 <p>8× M8 Art.-Nr. E0295</p>	 <p>1× Art.-Nr. E0292</p>	 <p>1× Art.-Nr. E0291</p>	 <p>4× Art.-Nr. E0294</p>	 <p>4× ø 8,4 mm Art.-Nr. E0780</p>	 <p>4× 4,5 x 25mm Art.-Nr. E0781</p>


BENÖTIGTES WERKZEUG / NEEDED TOOLS

<p>1</p>  <p>PH 1 × 100 PH 2 × 100</p>	<p>2</p>  <p>SW 7 SW 8 SW 13</p>
---	---

1.



2.  2x CL  2x CR



3. 8x M4 8x M4x10

② SW 7 ① PH2x100



4.



5.



6.



7.

10× M5

10× M5×10

10× 5,3MM

②



①



SW8 PH2×100



8.

8× M8

4× 8,4MM

10× 5,3MM

②



SW 13




9.



10.

2x M4 2x M4 x 10

② SW 7 ① PH1 x 100



11.

2x M4 2x M4 x 10

② SW 7 ① PH1 x 100




12.




13.

(X) 2x DL 4x M4 4x M4 x 10 (2) SW 7 (1) PH1 x 100



14.

(2) SW 7 (1) PH1 x 100



15.

4x M4

4x M4x10

2x DR

②

SW 7

①

PH 1x100



16.

2x KU4x16

1x Y

①

PH 1x100



17.




18.




19.





Durch den Einbauschränk anschrauben!
fix it through the cabinet!



Modell-Nr.

12160